

OPERATION

MANUAL

Work Top Refrigerator – CHILLER



Oberai Equipments

*Plot No 5, Konark Apartment,
Cuttack Road, Opp Falcon House
Bhubaneswar - 751006*

Mob: +91 9776800012 / +91 9776471111
Mob: +91 9437028164 / +91 9776010001

INTRODUCTION

OBERAI Professional Reach In Cabinets suitable for 2 x GN 1/1 sizes are built in SS304 with reliable EMERSON COMPRESSOR / LED temperature display, rounded internal edges for complete hygiene, removable magnetic gaskets for ease of cleaning, self closing doors heavy with door locks.

DOORS – 2 DOOR
NET WEIGHT – 180 KG
VOLUME – 600 IN LTRS.
SHELVES – 4 NOS.
TEMPERATURE RANGE - +2 TO +8 C
INPUT POWER – 600 WATT
REFRIGERANT – R134A

PURPOSE OF MANUAL

. FOR STORAGE PURPOSE OF ALL TYPES OF VEGETABLES , PANEER, GRAVY ITEMS AS REQUIRED

PROCEDURE FOR OPERATION

- . FIRST START THE CHILLER – 3 PIN PLUG INSERT AT POWER SUPPLY
- . POWER ON WILL DISPLAY ON DIGITAL TEMPERATURE CONTROLLER FITTED AT TOP COVER OF FRIDGE WITH 2 NOS. LED INDICATOR LIGHT WILL BLINK.
- . FIRST START THE TEMPERATURE SHOWS 30-25 DEGREE ON DISPLAY (RED LIGHT) AFTER HALF AN HOUR RUNNING THE TEMPERATURE DECREASES TO 5 DEGREE THEN SETTING DONE IT WILL AUTOCUT (COMPRESSOR STOPS) THEN THE TEMPERATURE COMES TO 11 TO 12 AGAIN COMPRESSOR STARTS IT WILL COME TO 5 DEGREE – LIKE THIS ITS WILL FUNCTION